



# Accura<sup>®</sup> ABS White (SL 7810)

ABS Class

Rigid and tough white plastic to simulate and replace CNC-machined ABS articles

## Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	46-48	6670-6960
Tensile Modulus (MPa/KSI)	ASTM D 638	2290-2400	332-348
Elongation at Break (%)	ASTM D 638	8-14	8-14
Flexural Strength (MPa/PSI)	ASTM D 790	74-76	10730-11020
Flexural Modulus (MPa/KSI)	ASTM D 790	2040-2120	296-307
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256	24-47	0.45-0.88
Heat Deflection Temperature	ASTM D 648 @ 66 PSI	51 °C	124 °F
Coefficient of Thermal Expansion (CTE)	ASTM E 831-93 25-50 °C	96	53
Glass Transition (Tg)	DMA, E''	63 °C	145 °F
Hardness, Shore D		86	86

## Features

- Rigid and tough
- Functional assemblies
- Short-run production parts

## Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	200 cps
Penetration Depth (Dp)		5.6 mils
Critical Exposure (Ec)		9.9 mJ/cm <sup>2</sup>
Color		White
Solid Density	@ 25 °C (77 °F)	1.16 g/cm <sup>3</sup>
Liquid Density	@ 25 °C (82 °F)	1.13 g/cm <sup>3</sup>



[www.3dsystems.com](http://www.3dsystems.com)

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, and Accura are registered trademarks of 3D Systems, Inc.