

# Accura<sup>®</sup> PP White (SL 7811)

PP Class

Flexible and tough plastic to simulate and replace CNC-machined white polypropylene articles

## Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	40-42	5800-6090
Tensile Modulus (MPa/KSI)	ASTM D 638	2030-2230	294-323
Elongation at Break (%)	ASTM D 638	7-13 %	7-13 %
Flexural Strength (MPa/PSI)	ASTM D 790	64-66	9280-9570
Flexural Modulus (MPa/KSI)	ASTM D 790	1960-2060	284-299
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256	42-59	0.78-1.10
Heat Deflection Temperature	ASTM D 648 @ 66 PSI	47 °C	117 °F
Coefficient of Thermal Expansion ( $\mu\text{m}/\text{m}\cdot\text{°C}$ / $\mu\text{m}/\text{in}\cdot\text{°F}$ )	ASTM E 831-93 25-50 °C 50-100 °C	92 $\mu\text{m}/\text{m}\cdot\text{°C}$ 207 $\mu\text{m}/\text{m}\cdot\text{°C}$	51 $\mu\text{in}/\text{in}\cdot\text{°F}$ 115 $\mu\text{in}/\text{in}\cdot\text{°F}$
Glass Transition (Tg)	DMA, E''	56 °C	133 °F
Hardness, Shore D		86	86

## Features

- Flexible and tough
- Snap fit assemblies
- Master patterns for vacuum casting
- Durable functional prototypes

## Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	210 cps
Penetration Depth (Dp)		5.25 mils
Critical Exposure (Ec)		10.97 mJ/cm <sup>2</sup>
Color		White
Solid Density	@ 25 °C (77 °F)	1.15 g/cm <sup>3</sup> at 25 °C
Liquid Density	@ 25 °C (82 °F)	1.11 g/cm <sup>3</sup> at 25 °C



[www.3dsystems.com](http://www.3dsystems.com)

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo and Accura are registered trademarks of 3D Systems, Inc.