

# VisiJet® M2R-TN

## Production Rigid

Rigid general-purpose plastic with opaque, high visual contrast, tan-colored finish delivering a balance of strength and elongation with a moderate to high HDT

ProJet MJP 2500

Similar to the VisiJet M2R-BK (black), the VisiJet M2R-TN has a higher tensile strength and modulus properties over standard VisiJet M2 materials. It is a stronger and stiffer plastic that is good for a broad range of concept models and functional prototypes. It has high feature fidelity, sharp corners and edges, and smooth surface finish. It is a general-purpose material with high accuracy and high visual contrast color suitable for general prototyping, dental mockups, and dental castings.



*Note: Not all products and materials are available in all countries — please consult your local sales representative for availability.*

### APPLICATIONS

- Simultaneous printing of dental mockups and flask casting patterns
- Ideal material for standard and Digital Silicone Tooling using the EggShell method
- Opaque functional prototypes and some end-use parts
- Rapid prototyping of plastic injection molded thermoplastic parts
- Able to be drilled, tapped, and machined
- Functional printed assemblies and injection molded screw bosses
- Functional printed screw-threads and thin walls
- Painted business/marketing collateral, prototypes, and mockups

### BENEFITS

- High fidelity fine features, sharp edges, and high accuracy
- Exceptional smooth and consistent surface finish
- High contrast tan color for easy visualization of surface detail
- No surface cure inhibition of paints or silicones. No sanding required.
- Excellent for painting. Ideal for eggshell molding applications.

### FEATURES

- Moderate/high strength and stiffness, 6-12% elongation
- Able to make extremely small and complex structures
- High accuracy and watertight
- Biocompatible USP Class VI

## MATERIAL PROPERTIES

The full suite of mechanical properties is given per ASTM and ISO standards where applicable. Properties like flammability, dielectric properties, and 24-hour water absorption are also provided for better understanding of material capabilities to help design decisions using the material. All parts are conditioned per ASTM recommended standards for a minimum of 40 hrs at 23°C, 50% RH.


Solid material properties reported were printed along the vertical axis (ZX-orientation). As detailed in the Isotropic Properties section, Multijet Printing (MJP) material properties are relatively uniform across print orientations. Parts do not need to be oriented in a particular direction to exhibit these properties.

LIQUID MATERIAL						
MEASUREMENT	CONDITION/METHOD	METRIC		ENGLISH		
Color		Tan				
SOLID MATERIAL						
METRIC	ASTM METHOD	METRIC	ENGLISH	ISO METHOD	METRIC	ENGLISH
PHYSICAL				PHYSICAL		
Solid Density	ASTM D792	1.16 g/cm <sup>3</sup>	0.04 lb/in <sup>3</sup>	ISO 1183	1.16 g/cm <sup>3</sup>	0.04 lb/in <sup>3</sup>
24 Hour Water Absorption	ASTM D570	≤0.5 %	≤0.5 %	ISO 62	≤0.5 %	≤0.5 %
MECHANICAL				MECHANICAL		
Tensile Strength Ultimate	ASTM D638	67 MPa	9700 psi	ISO 527 -1/2	60 MPa	8700 psi
Tensile Strength at Yield	ASTM D638	67 MPa	9700 psi	ISO 527 -1/2	N/A	N/A
Tensile Modulus	ASTM D638	3000 MPa	440 ksi	ISO 527 -1/2	2700 MPa	386 ksi
Elongation at Break	ASTM D638	4.0 %	4.0 %	ISO 527 -1/2	3.1 %	3.1 %
Elongation at Yield	ASTM D638	3.6 %	3.6 %	ISO 527 -1/2	N/A	N/A
Flex Strength	ASTM D790	100 MPa	14700 psi	ISO 178	100 MPa	13900 psi
Flex Modulus	ASTM D790	3100 MPa	450 ksi	ISO 178	3300 MPa	473 ksi
Izod Notched Impact	ASTM D256	14 J/m	0.3 ft-lb/in	ISO 180-A	1.9 J/m <sup>2</sup>	0.9 ft-lb/in <sup>2</sup>
Izod Unnotched Impact	ASTM D4812	120 J/m	2 ft-lb/in	ISO 180-U		
Shore Hardness	ASTM D2240	83 D	83 D	ISO 7619	83 D	83 D
THERMAL				THERMAL		
Tg (DMA, E")	ASTM E1640 (E"at 1C/min)	58 °C	136 °F	ISO 6721-1/11 (E"at 1C/min)	58 °C	136 °F
HDT @ 0.455 MPa/66 PSI	ASTM D648	70 °C	158 °F	ISO 75- 1/2 B	65 °C	149 °F
HDT @ 1.82 MPa/264 PSI	ASTM D648	58 °C	136 °F	ISO 75-1/2 A	53 °C	127 °F
CTE below Tg	ASTM E831	74 ppm/°C	41ppm/°F	ISO 11359-2	74 ppm/K	41 ppm/F
CTE above Tg	ASTM E831	170 ppm/°C	95 ppm/°F	ISO 11359-2	170 ppm/K	95 ppm/F
UL Flammability	UL94	HB	HB			
ELECTRICAL				ELECTRICAL		
Dielectric Strength (kV/mm) @ 3.0 mm thickness	ASTM D149	15.1				
Dielectric Constant @ 1 MHz	ASTM D150	3.14				
Dissipation Factor @ 1 MHz	ASTM D150	0.018				
Volume Resistivity (ohm-cm)	ASTM D257	7.16E+15				

## ISOTROPIC PROPERTIES

MJP technology prints parts that are generally isotropic in mechanical properties meaning the parts printed along either the XYZ axis will give similar results.


Parts do not need to be oriented to get the highest mechanical properties, further improving the degree of freedom for part orientation for mechanical properties.



SOLID MATERIAL								
METRIC	METHOD	METRIC						
MECHANICAL								
		XY	XZ	YX	YZ	Z45	ZX	ZY
Tensile Strength Ultimate	ASTM D638 Type IV	67 MPa	64 MPa	65 MPa	61 MPa	65 MPa	25 MPa	34 MPa
Tensile Strength at Yield	ASTM D638 Type IV	67 MPa	64 MPa	N/A	63 MPa	65 MPa	N/A	N/A
Tensile Modulus	ASTM D638 Type IV	3000 MPa	2800 MPa	2900 MPa	2800 MPa	2600 MPa	2800 MPa	2700 MPa
Elongation at Break	ASTM D638 Type IV	4 %	5.8 %	4.2 %	4.5 %	4.3 %	1 %	1.4 %
Elongation at Yield	ASTM D638 Type IV	3.6 %	4.1 %	N/A	4 %	4.1 %	N/A	N/A
Flex Strength	ASTM D790	100 MPa	87 MPa	99 MPa	80 MPa	86 MPa	56 MPa	44 MPa
Flex Modulus	ASTM D790	3100 MPa	2400 MPa	2900 MPa	2300 MPa	2600 MPa	2400 MPa	2200 MPa
Izod Notched Impact	ASTM D256	14 J/m	14 J/m	14 J/m	15 J/m	13 J/m	14 J/m	13 J/m
Shore Hardness	ASTM D2240	83 D	80 D	80 D	81 D	81 D	83 D	81 D

## STRESS-STRAIN CURVE

The graph represents the Stress-Strain curve for Visijet M2R-TN per ASTM D638 testing.







## LONG TERM ENVIRONMENTAL STABILITY

Visijet M2R-TN is engineered to give long term environmental UV and humidity stability. This means the material is tested for the ability to retain a high percent of the initial mechanical properties over a given period of time. **Actual data value is on Y-axis, and data points are % of initial value.**





**INDOOR STABILITY:** Tested per ASTM D4329 standard method.

INDOOR STABILITY



**OUTDOOR STABILITY:** Tested per ASTM G154 standard method.

OUTDOOR STABILITY



## AUTOMOTIVE FLUID COMPATIBILITY





The compatibility of a material with hydrocarbons and cleaning chemicals is critical to part application. Visijet M2R-TN parts were tested for sealed and surface contact compatibility per USCAR2 test conditions. The fluids below were tested in two different ways per the specs:

- Immersed for 7-days, followed by mechanical property comparison.
- Immersed for 30-minutes, followed by mechanical property comparison to 7-day data.

**Data reflects the measured value of properties over that period of time.**

AUTOMOTIVE FLUIDS		
FLUID	SPECIFICATION	TEST TEMP °C
Gasoline	ISO 1817, liquid C	23 ± 5
Diesel Fuel	905 ISO 1817, Oil No. 3 + 10% p-xylene*	23 ± 5
Engine Oil	ISO 1817, Oil No. 2	50 ± 3
Ethanol	85% Ethanol + 15% ISO 1817 liquid C*	23 ± 5
Power Steering Fluid	ISO 1917, Oil No. 3	50 ± 3
Automotive Transmission Fluid	Dexron VI (North American specific material)	50 ± 3
Engine Coolant	50% ethylene glycol + 50% distilled water*	50 ± 3
Brake Fluid	SAE RM66xx (Use latest available fluid for xx)	50 ± 3
Diesel Exhaust Fluid (DEF)	API certified per ISO 22241	23 ± 5

\*Solutions are determined as percent by volume



## CHEMICAL COMPATIBILITY





The compatibility of a material with cleaning chemicals is critical to part application. Visijet M2R-TN parts were tested for sealed and surface contact compatibility per ASTM D543 test conditions. The fluids below were tested in two different ways per the specs:

- Immersed for 7-days, followed by mechanical property comparison.
- Immersed for 30-minutes, followed by mechanical property comparison to 7-day data.

Data reflects the measured value of properties over that period of time.

\*Denotes materials did not go through 7-day soak conditioning.

CHEMICAL COMPATIBILITY
6.3.3 Acetone
6.3.12 Detergent Solution, Heavy Duty
6.3.23 Hydrochloric Acid (10%)
6.3.38 Sodium Carbonate Solution (20%)
6.3.44 Sodium Hypochlorite Solution
6.3.46 Sulfuric Acid (30%)
6.3.42 Sodium Hydroxide Soln (10%)
6.3.15 Distilled Water



## BIOCOMPATIBILITY STATEMENT

Visijet M2R-TN material printed in a ProJet 2500 has met the requirements of USP Class VI testing. Based on these results, 3D Systems expects that similar articles made from this material will meet the compliance requirements of USP Class VI when the produced parts are cleaned using the methods described in the User Guide.

It is the responsibility of each customer to independently determine that use of Visijet M2R-TN material for their specific application is safe, lawful and technically suitable. Customers should conduct their own testing to ensure compliance with any specific requirements. 3D Systems recommends that customers re-verify material suitability for applications requiring USP Class VI compliance no less frequently than every two years from the date of this publication due to potential changes in the law, regulations, material formulation or manufacturing methods.

For additional information about Visijet M2R-TN material, please contact your local sales representative.